

Product data sheet

Characteristics

1260025

Thorsman - TMX-8xM4 - cavity fixing - with threaded screw - set of 100



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TMX
Provided equipment	Threaded screw
Mounting support	High load installation in board material - thickness: 5...15 mm
Device application	5...15 mm high load installation in board material
Mounting support	Wall mounted
Thread type	M4
Screw diameter	4 mm
Screw length	40 mm
Shape of screw head	Cross slotted Combi-head
Screwdriver shape	Philips
Drilling diameter	8 mm
Colour tint	Grey Metal

Complementary

Quantity per set	Set of 100
Net weight	0.0072 kg

Environment

Material	Screw: steel electroplated Cavity fixing: sheet metal electroplated
Practical load capacity	Shear: 200 N 2.5) Pull-out load: 140 N 3)
Thickness	0...18 mm fixture
Environmental characteristic	Fire resistance
Ambient air temperature for operation	-40...80 °C
Diameter	14 mm
Length	47 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	6.0 g
Package 1 Height	1.1 cm
Package 1 width	1.1 cm
Package 1 Length	3.9 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	100
Package 2 Weight	686.0 g
Package 2 Height	10.6 cm

Package 2 width	8.2 cm
Package 2 Length	10.6 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	1800
Package 3 Weight	13.058 kg
Package 3 Height	14.4 cm
Package 3 width	27.4 cm
Package 3 Length	66.0 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------