

Product data sheet

Characteristics

1260140

Thorsman - TMX-12xM6 - cavity fixing - with threaded screw - set of 50



Main

Range of product	Thorsman
Product or component type	Cavity fixing
Device short name	TMX
Provided equipment	Threaded screw
Mounting support	High load installation in board material - thickness: 3...16 mm
Device application	3...16 mm high load installation in board material
Mounting support	Wall mounted
Thread type	M6
Screw diameter	6 mm
Screw length	57 mm
Shape of screw head	Cross slotted Combi-head
Screwdriver shape	Philips
Drilling diameter	12 mm
Colour tint	Metal Grey

Complementary

Quantity per set	Set of 50
Net weight	0.0212 kg

Environment

Material	Screw: steel electroplated Cavity fixing: sheet metal electroplated
Practical load capacity	Shear: 450 N 2.5) Pull-out load: 180 N 3)
Thickness	0...25 mm fixture
Environmental characteristic	Fire resistance
Ambient air temperature for operation	-40...80 °C
Diameter	18 mm
Length	62 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	6.1 cm
Package 1 Length	1.4 cm
Package 1 Weight	20 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	10.6 cm
Package 2 Width	8.2 cm

Package 2 Length	10.6 cm
Package 2 Weight	1.112 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	900
Package 3 Height	15 cm
Package 3 Width	27 cm
Package 3 Length	65 cm
Package 3 Weight	20 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------