

## Product data sheet

### Characteristics

# 1260B32

## LOCK RING BRASS COND 32MM



### Main

Range	Clipsal
Product or component type	Lockring
Accessory / separate part category	Fixing accessory
Range compatibility	Clipsal
Material	Brass



### Complementary

Diameter	External: 37 mm Thread: 32 mm
Height pitch dimension	1.5 mm
Thickness	5.5 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.012 kg
Package 1 Height	0.55 cm
Package 1 width	3.7 cm
Package 1 Length	3.7 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Weight	0.6 kg
Package 2 Height	7 cm
Package 2 width	10.7 cm
Package 2 Length	14 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	6.0 kg
Package 3 Height	22.6 cm
Package 3 width	19.1 cm
Package 3 Length	35.9 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>