

Product data sheet

Characteristics

13979

Weatherproof enclosure for modular device, Mureva Enclosure, 1x12 modules, 7 pre- cutouts, without terminal block

Main

Range	Mureva
Product name	Mureva Enclosure
Product or component type	Weatherproof enclosure
Enclosure type	Mini enclosure for modular device
Mounting plate description	Slotted

Complementary

Enclosure mounting	Surface
9 mm pitches	24
Number of 18 mm modules per row	12
Total number of 18 mm modules	12
Number of horizontal rows	1
Electrical insulation class	Double insulation Class II
Provided equipment	1 marking kit
Type of front cover	Transparent
Power dissipation in W	19 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	7
Locking options description	Optional keylock
Enclosure material	Self-extinguishing polymer
Width	267 mm
Height	200 mm
Depth	112 mm
Internal depth	56 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Environment

Standards	IEC 60695-2-1 IEC 60670 IEC 61439-3 EN 50262
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013

Overvoltage category	II
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.4 cm
Package 1 Width	20.0 cm
Package 1 Length	26.6 cm
Package 1 Weight	810.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	22.0 cm
Package 2 Width	34.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.5 kg
Unit Type of Package 3	P12
Number of Units in Package 3	96
Package 3 Height	80.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	99.48 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
SCIP Number	5036b720-908f-495f-9f9e-e215274e05b0
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product
Take-back	No
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	5
Minimum percentage of recycled plastic content	24

Contractual warranty

Warranty	18 months
----------	-----------