

Product data sheet

Characteristics

1438-TR

Standard Series, Extension Socket, 250VAC,
10A, Quick Connect



Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	Transparent
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Colour code	TR
Marking	Without marking
Local signalling	Without light indicator
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	62 mm
Diameter	41 mm




Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	----------------------------------------------------------------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5 cm
Package 1 Width	7 cm
Package 1 Length	10 cm
Package 1 Weight	48.3 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations