

## Product data sheet

### Characteristics

# 1438HD-TR

## SOCKET CORD EXTENSION 10A H/D



### Main

Range of product	Standard Series
Product or component type	Socket-outlet
Colour	Transparent
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

### Complementary

Colour code	TR
Marking	Without marking
Local signalling	Without light indicator
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	62 mm
Diameter	41 mm

### Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	49.0 g
Package 1 Height	4 cm
Package 1 width	10 cm
Package 1 Length	17.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	550.0 g
Package 2 Height	8.4 cm
Package 2 width	12.65 cm
Package 2 Length	17 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Weight	11.0 kg
Package 3 Height	25.4 cm
Package 3 width	34.8 cm
Package 3 Length	44.5 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>