

Product data sheet

Characteristics

1439/4P-TR

PLUG TOP 10A 250V 4 PIN



Main

Range of product	Standard Series
Product brand	Clipsal

Complementary

[In] rated current	10 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Colour	Body: transparent
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Straight
Duration	7 h

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	54 g
Package 1 Height	45 mm
Package 1 width	50 mm
Package 1 Length	80 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.618 kg
Package 2 Height	92 mm
Package 2 width	154 mm
Package 2 Length	186 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	6.7 kg
Package 3 Height	182 mm
Package 3 width	308 mm
Package 3 Length	453 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile