

Product data sheet

Characteristics

1439/4P-TR

Standard Series, Plugs, Rewireable Plugs, Plug Rigid 500V 10A 4 PIN to Suit 413/4P TR



Main

Range of product	Standard Series
Product brand	Clipsal

Complementary

[In] rated current	10 A
[Ue] rated operational voltage	500 V 50/60 Hz conforming to EN 60309-2
Colour	Body: transparent
Material	Plastic
Connections - terminals	Screw terminal
Plug, socket, control station shape	Straight
Duration	7 h

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	5 cm
Package 1 Length	8 cm
Package 1 Weight	54 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.2 cm
Package 2 Width	15.4 cm
Package 2 Length	18.6 cm
Package 2 Weight	618 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	18.2 cm
Package 3 Width	30.8 cm
Package 3 Length	45.3 cm
Package 3 Weight	6.7 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile