

## Product data sheet

### Characteristics

# 15/2VN-WE

## SWITCHED SOCKET TWIN VERTICAL 10A NEON



### Main

Colour	White electric
Product brand	Clipsal
Range of product	Standard Series

### Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Mounting position	Vertical
Fixing mode	By screws
Local signalling	Indicator light
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

### Packing Units

Package 1 Weight	1.000 kg
Package 1 Height	14.000 mm
Package 1 width	73.000 mm
Package 1 Length	115.000 mm