

Product data sheet

Characteristics

1501550

Thorsman installation material, sleeve anchor 12x100, set of 30



Main

| | |
|---------------------------|-------------------|
| Range of product | Thorsman |
| Product or component type | Sleeve anchor |
| Mounting support | Brick Concrete |
| Drilling diameter | 12 mm |
| Threaded length | 100 mm |






Environment

| | |
|-------------------------------|-----------|
| Quantity per set | Set of 30 |
| Sale per indivisible quantity | 30 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 2.1 cm |
| Package 1 Width | 2.1 cm |
| Package 1 Length | 10.5 cm |
| Package 1 Weight | 83.7 g |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |