

Product data sheet

Characteristics

1511234

Thorsman installation material, hook anchor M8, set of 25



Main

Range of product	Thorsman
Mounting support	Wall Ceiling Floor
Thread type	M8

Complementary

Provided equipment	Washer Nut
--------------------	---------------

Environment

Quantity per set	Set of 25
Sale per indivisible quantity	25

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	2.8 cm
Package 1 Length	9.3 cm
Package 1 Weight	42 g
Unit Type of Package 2	BB1
Number of Units in Package 2	25
Package 2 Height	8.2 cm
Package 2 Width	10.3 cm
Package 2 Length	14 cm
Package 2 Weight	1.13 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Height	23.5 cm
Package 3 Width	30 cm
Package 3 Length	44.5 cm
Package 3 Weight	23.45 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations