

Product data sheet

Characteristics

15336

Acti9 - IH - mechanical time switch - 24 h - 150 h memory



Main

| | |
|---------------------------|------------------------|
| Range of product | Acti 9 |
| Product name | Acti 9 IH |
| Device short name | IH |
| Product or component type | Mechanical time switch |
| Number of channels | 1 |
| Function available | Manual time changeover |

Complementary

| | |
|--------------------------------|--|
| Device application | Building |
| Load type | Parallel-corrected fluorescent tube 5 x 58 W 4.7 µF Parallel-corrected fluorescent tube 7 x 40 W 7 µF Parallel-corrected fluorescent tube 2 x 100 W 18 µF 230 V AC halogen lamp 1000 W 230 V AC incandescent lamp 1000 W Fluocompact lamp 700 VA Compact fluorescent lamp 150 W LED lamp < 2 W 30 W LED lamp > 2 W 300 W |
| Cycle duration | 24 h |
| Maximum number of switchings | 48 on - 48 off |
| Minimum interval duration | 15 min |
| Type of setting | Manual time changeover |
| Measurement accuracy | +/- 1 s/day 20 °C |
| Power consumption in W | 0.5 W |
| Maximum switching current | 16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6 |
| [Ue] rated operational voltage | 230...240 V AC at 50...60 Hz |
| Battery life | 10 year(s) |
| Backup time | 150 h time and program saving |
| Mounting support | DIN rail |
| 9 mm pitches | 2 |
| Colour tint | White (RAL 9003) |
| Connections - terminals | Screw terminals |
| Width | 18 mm |
| Height | 90 mm |
| Depth | 66 mm |
| Net weight | 0.101 kg |

Environment

| | |
|---------------------------------------|-------------------|
| Ambient air temperature for operation | -10...50 °C |
| IP degree of protection | Terminals: IP20 B |

Packing Units

| | |
|------------------------------|------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 103 g |
| Package 1 Height | 2 cm |
| Package 1 width | 7 cm |
| Package 1 Length | 11 cm |
| Unit Type of Package 2 | S03 |
| Number of Units in Package 2 | 110 |
| Package 2 Weight | 11.964 kg |
| Package 2 Height | 30 cm |
| Package 2 width | 30 cm |
| Package 2 Length | 40 cm |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 880 |
| Package 3 Weight | 110.192 kg |
| Package 3 Height | 50 cm |
| Package 3 width | 80 cm |
| Package 3 Length | 120 cm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|