

Product data sheet

Characteristics

15D-WE

SWITCHED SOCKET SINGLE DOUBLE POLE

10A 250V



Main

Colour	White electric
Product brand	Clipsal
Range of product	Standard Series

Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	83 g
Package 1 Height	72 mm
Package 1 width	35 mm
Package 1 Length	115 mm

Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.45 kg
Package 2 Height	106 mm
Package 2 width	124 mm
Package 2 Length	142 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	9.2 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile