

Product data sheet

Characteristics

15D15-WE

SWITCHED SOCKET SINGLE DOUBLE POLE

15A 250V



Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	79 g
Package 1 Height	30 mm
Package 1 width	184 mm
Package 1 Length	115 mm
Unit Type of Package 2	BB1

Number of Units in Package 2	5
Package 2 Weight	0.452 kg
Package 2 Height	122 mm
Package 2 width	106 mm
Package 2 Length	140 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	4.7 kg
Package 3 Height	157 mm
Package 3 width	305 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile