

## Product data sheet

### Characteristics

# 15D2V-WE

## SWITCHED SOCKET TWIN DOUBLE POLE

### 10A 250V



#### Main

Colour	White electric
Product brand	Clipsal
Range of product	Standard Series

#### Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Mounting position	Vertical
Fixing mode	By screws
Local signalling	Without light indicator
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	97 mm

#### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

#### Packing Units

Package 1 Weight	0.160 kg
Package 1 Height	14.000 mm
Package 1 width	73.000 mm
Package 1 Length	115.000 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>