

Product data sheet

Characteristics

15DX-WE

SWITCHED SOCKET SINGLE DOUBLE POLE 10A EXTRA SWITCH



Main

Colour	White electric
Product brand	Clipsal
Range of product	Standard Series

Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	104 g
Package 1 Height	37 mm
Package 1 width	73 mm
Package 1 Length	115 mm

Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.582 kg
Package 2 Height	122 mm
Package 2 width	106 mm
Package 2 Length	142 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	5.2 kg
Package 3 Height	157 mm
Package 3 width	305 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile