

## Product data sheet

### Characteristics

# 15L-WE

## SOCKET SWITCHED SINGLE 10A 250V LIGHTING



### Main

|                           |                 |
|---------------------------|-----------------|
| Range of product          | Standard Series |
| Product or component type | Switched socket |
| Product brand             | Clipsal         |
| Colour                    | White electric  |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Control type                   | ON/OFF button           |
| Number of gangs                | 1 gang                  |
| Pin number                     | 3                       |
| Number of power socket outlets | 1                       |
| Actuator                       | Rocker Switch           |
| Fixing mode                    | By screws               |
| Local signalling               | Without light indicator |
| Mounting position              | Horizontal              |
| Material                       | PC (polycarbonate)      |
| Surface finish                 | Glossy                  |
| [Ue] rated operational voltage | 250 V AC                |
| [In] rated current             | 10 A                    |
| Depth                          | 14 mm                   |
| Length                         | 115 mm                  |
| Width                          | 73 mm                   |
| Fixing center                  | 84 mm                   |

### Environment

|           |  |
|-----------|--|
| Standards | AS/NZS 3100<br>AS/NZS 3112<br>AS/NZS 3133<br>AS/NZS 3000:approval number S/1 |
|-----------|--|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 3 cm    |
| Package 1 Width              | 7 cm    |
| Package 1 Length             | 11.5 cm |
| Package 1 Weight             | 81 g    |
| Unit Type of Package 2       | BB1     |

|                              |         |
|------------------------------|---------|
| Number of Units in Package 2 | 5       |
| Package 2 Height             | 11.7 cm |
| Package 2 Width              | 10.2 cm |
| Package 2 Length             | 13.8 cm |
| Package 2 Weight             | 460 g   |
| Unit Type of Package 3       | CAR     |
| Number of Units in Package 3 | 50      |
| Package 3 Height             | 15.7 cm |
| Package 3 Width              | 30.5 cm |
| Package 3 Length             | 44.5 cm |
| Package 3 Weight             | 4.6 kg  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |