

Product data sheet

Characteristics

15VN-WE

SINGLE SWITCHED SOCKET VERTICAL MOUNT 10A NEON



Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Mounting position	Vertical
Fixing mode	By screws
Local signalling	Indicator light
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Package 1 Weight	0.001 kg
Package 1 Height	14.000 mm
Package 1 width	73.000 mm
Package 1 Length	115.000 mm