

Product data sheet

Characteristics

15VXN-WE

SINGLE SWITCHED SOCKET VERTICAL MOUNT WITH EXTRA SWITCH NEON



Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Vertical
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	91.0 g
Package 1 Height	1.4 cm
Package 1 width	7.3 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Weight	455.0 g
Package 2 Height	11.7 cm
Package 2 width	10.2 cm
Package 2 Length	13.8 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	4550.0 g
Package 3 Height	15.7 cm
Package 3 width	30.5 cm
Package 3 Length	44.5 cm