

## Product data sheet

### Characteristics

# 15VXX-WE

## SOCKET SWITCHED SINGLE VERTICAL MOUNT WITH TWO EXTRA SWITCHES



### Main

Colour	White electric
Product brand	Clipsal
Range of product	Standard Series

### Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Mounting position	Vertical
Fixing mode	By screws
Local signalling	Without light indicator
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.14 kg
Package 1 Height	14 mm
Package 1 width	73 mm
Package 1 Length	115 mm

Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.7 kg
Package 2 Height	117 mm
Package 2 width	102 mm
Package 2 Length	138 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	7 kg
Package 3 Height	157 mm
Package 3 width	305 mm
Package 3 Length	445 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>