

## Product data sheet

### Characteristics

# 15XX-WE

## Single Switch Socket Outlet, 250V, 10A, Standard Size, 2 Removable Extra Switch



### Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	11.8 cm
Package 1 Length	7.1 cm
Package 1 Weight	104 g
Unit Type of Package 2	BB1

Number of Units in Package 2	5
Package 2 Height	12.4 cm
Package 2 Width	10.8 cm
Package 2 Length	14.6 cm
Package 2 Weight	582 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	25.4 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	12 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>