

Product data sheet

Characteristics

16/2-WE

Standard Series, Twin Switch Socket Outlet, 250V, 10A, Skirt Mount



Main

Range of product	Standard Series
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	18 mm
Length	168 mm
Width	45 mm
Fixing center	145 mm
Distance between centers	145 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	4.4 cm
Package 1 Length	16.8 cm
Package 1 Weight	118 g
Unit Type of Package 2	BB1

Number of Units in Package 2	5
Package 2 Height	7.4 cm
Package 2 Width	11.6 cm
Package 2 Length	20 cm
Package 2 Weight	654 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	25 cm
Package 3 Width	21.4 cm
Package 3 Length	33.8 cm
Package 3 Weight	6.6 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile