

Product data sheet

Characteristics

16/2F-WE

SWITCHED SOCKET TWIN 10A SKIRT STR



Main

Range of product	Standard Series
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	18 mm
Length	168 mm
Width	45 mm
Fixing center	145 mm
Distance between centers	145 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	120 g
Package 1 Height	28 mm
Package 1 width	45 mm
Package 1 Length	168 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Weight	1.274 kg
Package 2 Height	100 mm
Package 2 width	158 mm
Package 2 Length	190 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	12.2 kg
Package 3 Height	210 mm
Package 3 width	348 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile