

Product data sheet

Characteristics

16/2MF-WE

SWITCHED SOCKET TWIN 10A SKIRT DUCT



Main

Colour	White electric
Product brand	Clipsal
Range of product	Standard Series

Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	18 mm
Length	156 mm
Width	44 mm
Fixing center	136 mm
Distance between centers	145 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	116 g
Package 1 Height	32 mm
Package 1 width	45 mm
Package 1 Length	160 mm
Unit Type of Package 2	BB1

Number of Units in Package 2	5
Package 2 Weight	0.64 kg
Package 2 Height	72 mm
Package 2 width	117 mm
Package 2 Length	154 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	6.4 kg
Package 3 Height	226 mm
Package 3 width	191 mm
Package 3 Length	359 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile