

Product data sheet

Characteristics

16/2MF-WE

Standard Series, Twin Switch Socket Outlet, 250V, 10A, Skirt Mount for Ducting, Straight Side



Main

Range of product	Standard Series
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	18 mm
Length	156 mm
Width	44 mm
Fixing center	136 mm
Distance between centers	145 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	4.5 cm
Package 1 Length	16 cm

Package 1 Weight	116 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	7.2 cm
Package 2 Width	11.7 cm
Package 2 Length	15.4 cm
Package 2 Weight	640 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	22.6 cm
Package 3 Width	19.1 cm
Package 3 Length	35.9 cm
Package 3 Weight	6.4 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile