

## Product data sheet

### Characteristics

# 16/2MF1510-WE

Standard Series, Twin Switch Socket Outlet, 250V, 10/15A, Skirt Mount for Ducting, Straight Side



### Main

Range of product	Standard Series
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A 10 A
Depth	18 mm
Length	156 mm
Width	44 mm
Fixing center	136 mm
Distance between centers	145 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.5 cm
Package 1 Length	15.5 cm

Package 1 Weight	116 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	7.4 cm
Package 2 Width	12 cm
Package 2 Length	16.5 cm
Package 2 Weight	630 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	22.6 cm
Package 3 Width	19.1 cm
Package 3 Length	35.9 cm
Package 3 Weight	7 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>