

## Product data sheet

### Characteristics

# 16X-WE

Standard Series, Single Switch Socket Outlet, 250V, 10A, Skirt Mount, Removable Extra Switch



### Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	14 mm
Length	98 mm
Width	45 mm
Fixing center	78 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---------------------------------------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.7 cm
Package 1 Width	12.8 cm
Package 1 Length	3 cm
Package 1 Weight	81 g

Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	8.5 cm
Package 2 Width	9.7 cm
Package 2 Length	15 cm
Package 2 Weight	5 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	23.7 cm
Package 3 Width	20.3 cm
Package 3 Length	30 cm
Package 3 Weight	50 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>