

Product data sheet

Characteristics

180HD40

Clipsal - Cable Management, Fixing Accessories, Metal, Saddles, 40mm Hot Dip Galvanised



Main

Product brand	Clipsal
---------------	---------

Complementary

Diameter	40 mm
Material	Steel
Surface treatment	Hot-dip galvanized
Length	74 mm
Width	32 mm
Height	41 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.9 cm
Package 1 Width	3.2 cm
Package 1 Length	7.6 cm
Package 1 Weight	40 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	105 cm
Package 2 Width	190 cm
Package 2 Length	215 cm
Package 2 Weight	2.15 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	250
Package 3 Height	230 cm
Package 3 Width	305 cm
Package 3 Length	440 cm
Package 3 Weight	10.75 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations