

Product data sheet

Characteristics

193/20-1

PNL MOUNT OUTLET 20A 1 - 2MM

Main

Range of product	PDL
Colour	White
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Complete housing

Complementary

Marking	Without marking
Local signalling	Without light indicator
Mounting support	panel
[In] rated current	20 A
[Ue] rated operational voltage	230...240 V AC
Network frequency	50 Hz
Diameter	32 mm



Environment

Standards	AS/NZS 3100 AS/NZS 3112
-----------	----------------------------

Packing Units

Package 1 Weight	0.020 kg
------------------	----------

Offer Sustainability

EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.