

Product data sheet

Characteristics

2010L-WE

SOCKET SWITCHED AUTO SWITCHED SINGLE 10A LIGHTING



Main

Range of product	Series 2000
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Indicator light
Fixing mode	By screws
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	31 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	90.0 g
Package 1 Height	3 cm
Package 1 width	7.5 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	514.0 g
Package 2 Height	8.8 cm
Package 2 width	12.6 cm
Package 2 Length	18 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50

Package 3 Weight	4.5 kg
Package 3 Height	18.2 cm
Package 3 width	30.8 cm
Package 3 Length	45.3 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile