

Product data sheet

Characteristics

2010N-WE

SOCKET SWITCHED AUTO SWITCHED SINGLE 10A NEON



Main

Range of product	Series 2000
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1

Complementary

Colour code	WE
Protection type	Fingersafe
Local signalling	Without light indicator
[In] rated current	10 A
[Ue] rated operational voltage	250 V AC
Depth	31 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	105 g
Package 1 Height	3.1 cm
Package 1 width	7.6 cm
Package 1 Length	11.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	525 g
Package 2 Height	11.9 cm
Package 2 width	8.3 cm
Package 2 Length	17.9 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	5.25 kg

Package 3 Height	18.2 cm
Package 3 width	30.8 cm
Package 3 Length	45.3 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile