

## Product data sheet

### Characteristics

# 2015/2VN-WE

## SWITCHED SOCKET TWIN VERTICAL 10A NEON



### Main

Range of product	Series 2000
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Vertical
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	12 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.136 kg
Package 1 Height	1.2 cm
Package 1 width	7.6 cm
Package 1 Length	11.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Weight	0.68 kg
Package 2 Height	12.2 cm
Package 2 width	14.1 cm
Package 2 Length	16.1 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	13.6 kg
Package 3 Height	25.4 cm
Package 3 width	34.8 cm
Package 3 Length	44.5 cm