

## Product data sheet

### Characteristics

# 2015/2VS-WE

## SWITCHED SOCKET TWIN VERTICAL 10A SHUTTER



### Main

|                  |                |
|------------------|----------------|
| Range of product | Series 2000    |
| Product brand    | Clipsal        |
| Colour           | White electric |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Control type                   | ON/OFF button           |
| Number of gangs                | 2 gangs                 |
| Pin number                     | 3                       |
| Number of power socket outlets | 2                       |
| Actuator                       | Switch<br>Rocker        |
| Fixing mode                    | By screws               |
| Local signalling               | Without light indicator |
| Mounting position              | Vertical                |
| Material                       | Plastic                 |
| Surface finish                 | Glossy                  |
| [Ue] rated operational voltage | 250 V AC                |
| [In] rated current             | 10 A                    |
| Depth                          | 12 mm                   |
| Length                         | 116 mm                  |
| Width                          | 76 mm                   |
| Fixing center                  | 84 mm                   |

### Environment

|           |   |
|-----------|---|
| Standards | AS/NZS 3100<br>AS/NZS 3112<br>AS/NZS 3133:approval number S/1 |
|-----------|---|

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Weight             | 0.136 kg |
| Package 1 Height             | 1.2 cm   |
| Package 1 width              | 7.6 cm   |
| Package 1 Length             | 11.6 cm  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>                           |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |