

Product data sheet

Characteristics

2015D20-WE

SOCKET SWITCHED SINGLE DOUBLE POLE

20A 250V



Main

Range of product	Series 2000
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	20 A
Depth	12 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	127 g
Package 1 Height	6 cm
Package 1 width	8 cm
Package 1 Length	12 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Weight	748 g
Package 2 Height	10.2 cm
Package 2 width	14.4 cm
Package 2 Length	24.2 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	50 kg
Package 3 Height	25.4 cm
Package 3 width	34.8 cm
Package 3 Length	44.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile