

## Product data sheet

### Characteristics

# 2015DN20-WE

## SOCKET SWITCHED SINGLE DOUBLE POLE

## 20A NEON



### Main

Colour	White electric
Product brand	Clipsal
Range of product	Series 2000

### Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Indicator light
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	20 A
Depth	12 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---------------------------------------------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg
Package 1 Height	12 mm
Package 1 width	76 mm
Package 1 Length	116 mm
Unit Type of Package 2	BB1

Number of Units in Package 2	5
Package 2 Weight	5 kg
Package 2 Height	95 mm
Package 2 width	138 mm
Package 2 Length	239 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	50 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>