

Product data sheet

Characteristics

2015V15N-WE

Clipsal 2000 Series Single Switch Socket Outlet 250V, 15A, Vertical



Main

Range of product	Series 2000
Product or component type	Switched socket
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Vertical
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	12 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	1.2 cm
Package 1 Width	7.6 cm
Package 1 Length	11.6 cm
Package 1 Weight	0.096 kg
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	10

Package 2 Height	12.2 cm
Package 2 Width	14.1 cm
Package 2 Length	16.1 cm
Package 2 Weight	960 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	25.4 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	9.6 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile