

Product data sheet

Characteristics

2015XSM-WE

SOCKET SWITCHED SINGLE SURFACE WITH REMOVABLE EXTRA SWITCH



Main

Range of product	Series 2000
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	30 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg
Package 1 Height	30 mm
Package 1 width	76 mm
Package 1 Length	116 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5

Package 2 Weight	5 kg
Package 2 Height	119 mm
Package 2 width	83 mm
Package 2 Length	179 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	100 kg
Package 3 Height	305 mm
Package 3 width	296 mm
Package 3 Length	436 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile