

Product data sheet

Characteristics

2025-WE

SWITCHED SOCKET TWIN 10A 250V



Main

Range of product	Series 2000
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	13 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Product certifications	RCM
Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.3 cm
Package 1 Width	7.6 cm
Package 1 Length	11.6 cm
Package 1 Weight	116 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Height	12.4 cm
Package 2 Width	14.6 cm
Package 2 Length	16.4 cm
Package 2 Weight	1.16 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	26.2 cm
Package 3 Width	35 cm
Package 3 Length	44 cm
Package 3 Weight	11.662 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile