

## Product data sheet

### Characteristics

# 2025/15-WE

## Twin Switch Socket Outlet, 2000 Series, 250V, 15A



### Main

Range of product	Series 2000
Product or component type	Switched socket
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Rocker Switch
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	28 mm
Length	116 mm
Width	76 mm
Mounting Centers	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	12.0 cm
Package 1 Length	7.7 cm
Package 1 Weight	112.0 g
Unit Type of Package 2	CAR

Number of Units in Package 2	100
Package 2 Height	25.4 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	11.2 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	3200
Package 3 Height	101.6 cm
Package 3 Width	116.5 cm
Package 3 Length	116.5 cm
Package 3 Weight	358.4 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations