

## Product data sheet

### Characteristics

# 2025H2-WE

## SOCKET HORIZONTAL TWIN 2 GANG AND SURROUND



### Main

Range of product	Gangbusters
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	4 gangs
Pin number	3
Number of power socket outlets	4
Actuator	Rocker Switch
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	255.6 g
Package 1 Height	25 mm
Package 1 width	75 mm
Package 1 Length	232 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	1.336 kg
Package 2 Height	37 mm
Package 2 width	252 mm

Package 2 Length	444 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	14 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>