

Product data sheet

Characteristics

2025L-WE

SWITCHED SOCKET TWIN 10A 250V LTG



Main

Range of product	Series 2000
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric
Socket additional information	Round earth

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	111.0 g
Package 1 Height	2.5 cm
Package 1 width	7.5 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.186 kg

Package 2 Height	13 cm
Package 2 width	14.6 cm
Package 2 Length	16.7 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	5.55 kg
Package 3 Height	15.7 cm
Package 3 width	30.5 cm
Package 3 Length	44.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile