

Product data sheet

Characteristics

2025SF-WE

2000 Series, Surge Protected Socket Outlet 1 Pole, 250V, 10A



Main

Range of product	Series 2000
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Indicator light
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	45 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.9 cm
Package 1 Width	10.0 cm
Package 1 Length	14.8 cm
Package 1 Weight	181.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	20

Package 2 Height	23.3 cm
Package 2 Width	29.0 cm
Package 2 Length	29.8 cm
Package 2 Weight	3.9 kg

Offer Sustainability

EU RoHS Directive

Compliant  [EU RoHS Declaration](#)