

## Product data sheet

### Characteristics

# 2025VS-WE

## SWITCHED SOCKET TWIN VERTICAL 10A SHUTTER



### Main

Colour	White electric
Product brand	Clipsal
Range of product	Series 2000

### Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Mounting position	Vertical
Fixing mode	By screws
Local signalling	Without light indicator
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.12 kg
Package 1 Height	28 mm
Package 1 width	76 mm
Package 1 Length	116 mm
Unit Type of Package 2	BB1

Number of Units in Package 2	10
Package 2 Weight	1.2 kg
Package 2 Height	122 mm
Package 2 width	141 mm
Package 2 Length	161 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	12 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>