

## Product data sheet

### Characteristics

# 2031D32-WE

## 2000 Series, Electric Range Switches 415V 32A Double Pole



### Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate

### Complementary

Switch function	2-pole
Number of rocker	1
Number of poles	2
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	415 V AC
Rated current	32 A
Marking	Without marking
Actuator	Rocker

### Environment

Standards	AS/NZS 3133
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12 cm
Package 1 Width	4 cm
Package 1 Length	18 cm
Package 1 Weight	124 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	122 cm
Package 2 Width	154 cm
Package 2 Length	164 cm
Package 2 Weight	1.312 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	254 cm
Package 3 Width	348 cm

Package 3 Length	445 cm
Package 3 Weight	12.4 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>