

Product data sheet

Characteristics

2031H66-WE

Flush Switch, 2000 Series, 1 Gang, 250VAC, 10A, Series 2000, Weatherproof, Horizontal, IP66

Main

Range of product	Series 2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate

Complementary

Installation Type	Flush
Number Of Switches	1
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A 10 AX, fluorescent lamp
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	2-way 1-way

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	8.0 cm
Package 1 Length	12.5 cm
Package 1 Weight	110.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Height	237 mm
Package 2 Width	203 mm
Package 2 Length	300 mm
Package 2 Weight	2.75 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	1600
Package 3 Weight	172.8 kg

Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	Yes
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Take-back	No