

Product data sheet

Characteristics

2031H66-WE

SWITCH 1 GANG HORIZONTAL 10A IP66



Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	2-way 1-way
Number of rocker	1
Device mounting	Flush
Fixing mode	By screws
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A 10 AX, fluorescent lamp
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	110.0 g
Package 1 Height	6 cm
Package 1 width	8 cm
Package 1 Length	12.5 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Weight	2.75 kg
Package 2 Height	237 mm
Package 2 width	203 mm
Package 2 Length	300 mm
Unit Type of Package 3	PAL
Number of Units in Package 3	1600
Package 3 Weight	172.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile