

Product data sheet

Characteristics

2031VCS-WE

SOCKET OUTLET 32A COOKER



Main

Range of product	Series 2000
Product or component type	Socket-outlet
Colour	White electric
Product brand	Clipsal
Quantity per set	Set of 1
Cover type	Full cover plate

Complementary

Colour code	WE
Marking	Without marking
Local signalling	Without light indicator
[In] rated current	32 A
[Ue] rated operational voltage	250 V AC
Depth	43 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3112 AS 3100 AS 3109 AS/NZS 3122:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.6 cm
Package 1 Length	11.6 cm
Package 1 Weight	118.6 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	11.8 cm
Package 2 Width	14.1 cm
Package 2 Length	16.1 cm
Package 2 Weight	680 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	25.4 cm
Package 3 Width	34.8 cm

Package 3 Length	44.5 cm
Package 3 Weight	6.9 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile