

Product data sheet

Characteristics

2032VAPB-WE

SWITCH P/B 2GANG VERTICAL



Main

Range of product	Series 2000 Impress
Product or component type	Push-button
Colour	White electric
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Colour code	WE
Actuator	Push-button
Local signalling	Without light indicator
Fixing mode	By screws
Material	Plastic
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Depth	30 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm
Mounting position	Vertical

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.07 kg
Package 1 Height	30 mm
Package 1 width	76 mm
Package 1 Length	116 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.7 kg
Package 2 Height	122 mm
Package 2 width	154 mm
Package 2 Length	240 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	3.5 kg
Package 3 Height	238 mm
Package 3 width	342 mm
Package 3 Length	390 mm

Offer Sustainability

EU RoHS Directive

Under investigation

Environmental Disclosure

 [Product Environmental Profile](#)