

Product data sheet

Characteristics

2032VAPB-WE

SWITCH P/B 2GANG VERTICAL



Main

Range of product	Series 2000 Impress
Product or component type	Push-button
Colour	White electric
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Colour code	WE
Actuator	Push-button
Local signalling	Without light indicator
Fixing mode	By screws
Material	Plastic
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Depth	30 mm
Width	76 mm
Length	116 mm
Fixing center	84 mm
Mounting position	Vertical

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.07 kg
Package 1 Height	3 cm
Package 1 width	7.6 cm
Package 1 Length	11.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	700.0 g
Package 2 Height	12.2 cm
Package 2 width	15.4 cm
Package 2 Length	24 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	3.5 kg
Package 3 Height	23.8 cm
Package 3 width	34.2 cm
Package 3 Length	39 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile