

Product data sheet

Characteristics

2032VAPBL-WE

SWITCH PUSH BUTTON LED 2 GANG VERTICAL



Main

| | |
|---------------------------|-------------------------------------|
| Range of product | Impress Series 2000 |
| Product or component type | Push-button |
| Colour | White electric |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate |

Complementary

| | |
|--------------------------------|-----------------|
| Colour code | WE |
| Actuator | Push-button |
| Local signalling | Indicator light |
| Fixing mode | By screws |
| Material | Plastic |
| [Ue] rated operational voltage | 250 V AC |
| Inrush current | 20 A |
| Depth | 30 mm |
| Width | 76 mm |
| Length | 116 mm |
| Fixing center | 84 mm |
| Mounting position | Vertical |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 102 g |
| Package 1 Height | 50 mm |
| Package 1 width | 75 mm |
| Package 1 Length | 117 mm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 1.12 kg |
| Package 2 Height | 122 mm |
| Package 2 width | 154 mm |
| Package 2 Length | 240 mm |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 50 |
| Package 3 Weight | 5.6 kg |
| Package 3 Height | 238 mm |

| | |
|------------------|--------|
| Package 3 width | 342 mm |
| Package 3 Length | 390 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |